
# AMPOULE RIGID WITH RIGID BOTTOM



# **ZOOM**ON THE PRODUCT

## THE ALTERNATIVE to the glass ampoule

Easy and safe breakability: thanks to the ampoule patented by SERIPLAST, the risk of injury is eliminated

For aqueous formulations from 1 to 3000 centipoises









Possibility to simply use the ampoules in one shot or in several times, in this case close the ampoule with the breakable head

Packaging delivered in 2 parts (ampoule + rigid bottom)

#### **DISTRIBUTION**

Liquids Powders Granules









#### **DECORATION**

Screen (silk) printing Hot stamping



# AMPOULE RIGID WITH SOFT BOTTOM

## **ZOOM**ON THE PRODUCT

#### THE ALTERNATIVE to the glass ampoule

Ø 18











Nomac



10 ml

#### Easy and safe breakability:

thanks to the ampoule patented by SERIPLAST, the risk of injury is eliminated

For aqueous formulations from 1 to 3000 centipoises








Simple and precise use by pressure on the soft bottom

Possibility to simply use the ampoules in one shot or in several times, in this case close the ampoule with the breakable head

Packaging delivered in 2 parts (ampoule + soft bottom)

Possibility to have a nomad pack with a closure system



Available with different applicator tips adapted to your formulas

A - Integrated applicator tip

B - Headwear applicator tip

#### **DISTRIBUTION**

Liquids Serum Cream

Cream Powders








DECORATION
Screen (silk) printing

Hot stamping

## **AMPOULE** SQUEEZE-ME



## ZOOM

#### ON THE PRODUCT

#### THE ALTERNATIVE to the glass ampoule

Easy and safe breakability: thanks to the ampoule patented by SERIPLAST, the risk of injury is eliminated

For aqueous formulations from 1 to 10 000 centipoises











Possibility to have a nomad pack with a closure system

Possibility to simply use the ampoules in one shot or in several times, in this case close the ampoule with the breakable head

Simple and precise use by pressing the ampoule

Packaging delivered in 2 parts (ampoule + rigid bottom)

Liquids Serum Cream

**DISTRIBUTION** 

**Powders** 







**DECORATION** Screen (silk) printing Hot stamping

You can create your own artwork without technical limit.



Outflow Ø1,2



Outflow Ø2,8



A - Integrated applicator tip B - Headwear applicator tip

Available with different


applicator tips adapted

to your formulas

Possibility to have a nomad pack with a closure system

#### SOFT AMPOULE

TO BE WELDED



## ZOOM

#### ON THE PRODUCT

#### THE ALTERNATIVE to the glass ampoule

Easy and safe breakability: thanks to the ampoule

patented by SERIPLAST, the risk of injury is eliminated

For aqueous formulations from 1 to 100 000 centipoises







Possibility to have a nomad pack with a closure system

Available in micro roll-on Ø10 : steel ball, glass or plastic

Packaging delivered in 1 part Ø18 -Ø20 : with or without integrated applicator



Liquids Serum

Cream Powders









DECORATION

Screen (silk) printing Hot stamping

You can create your own artwork without technical limit.





 $\emptyset$ 2,8



Available with different applicator tips adapted to your formulas

A - Integrated applicator tip

B - Headwear applicator tip

## **AMPOULE** MICRO ROLL ON


Ø 10



1	n	n	١				
L	7				P	P	)
,					5	2	)

Simple and precise use with its integrated ball








## ZOOM ON THE PRODUCT


## THE ALTERNATIVE to the glass ampoule

Easy and safe breakability: thanks to the ampoule patented by SERIPLAST,

the risk of injury is eliminated

For aqueous formulations from 1 to 3000 centipoises





Available with different balls: glass, stainless steel or plastic

Packaging delivered in 2 parts (ampoule + rigid bottom)

#### **DISTRIBUTION**

Liquids Serum





**DECORATION** 

Screen (silk) printing Hot stamping

## **AMPOULE** HEADWEAR APPLICATOR ROLL-ON

Ø 18





#### Ø 18 RIGID WITH RIGID BOTTOM









## ZOOM

## ON THE PRODUCT

2 possibilities of use:

for single use: 1 applicator tip = 1 ampoule multiple use: 1 applicator tip = several ampoule

For aqueous formulations from 1 to 10000 centipoises

Packaging delivered in 1 part

Stainless steel ball or glass ball

- 1 Snap of the head of the ampoule
- 2 Assembling of the applicator roll-on
- **3** Unscrew the cap
- **4** Apply the formulation










## Ø 18 / Ø 20 : SQUEEZE-ME





## Ø 18 TO BE WELDED




#### **DISTRIBUTION**

Liquids Cream



#### **ATTRACTIVE**

AIRLESS - ATMOSPHERIC



#### Ø 32 ATMOSPHERIC


















Packaging delivered in 2 parts (a bottle and a pump assembly with assembled cap polished or frosted)

Possibility to have a bottle of recycled material

#### ZOOM

#### ON THE PRODUCT

Available in airless or atmospheric version Airless from 20ml to 65ml Atmosphérique from 30ml to 75ml

Dose of available pumps: 250µl

Seriplast Pump

Quick filling with its wide opening



**Atmospheric** 



#### **AIRLESS:**

Pump efficiency guarantee to the latter pressure it is used upside down or head up

Optimum use of the product, in case of very thick formulations, or sensitive to air

Possibility of using little or no preservatives

Product distribution with a viscosity from 3000 to 75000 centipoises

#### **ATMOSPHERIC:**

Product distribution with a viscosity from 1 to 30000 centipoises

Customizing the pumps with a wide range of options: curved collar (frosted or smooth), right, colored ring, various actuator, out-flow motor...

#### DISTRIBUTION

Cream Liquid Serum







## **DECORATION**

Screen (silk) printing Hot stamping



## ROLL ON

Ø32-Ø41





100 ml

125 ml

150 ml

△ PP 185

50 ml

50 ml

75 ml

101


## ZOOM ON THE PRODUCT

Product distribution with a viscosity from 3000 to 30000 centipoises

Customization roll-on pack with a wide range of bottles, polished and frosted caps: curved or straight

Natural or white ball





#### Quick filling with its wide opening

Packaging delivered in 2 parts (a bottle, an hopper assembly composed of a housing ball, a ball, and a srew cap)

#### **DISTRIBUTION**

Liquids Cream








#### **DECORATION**

Screen (silk) printing Hot stamping

#### **ARIANE**

## PUSH IT PACK: 2 FORMULATIONS TO MIX




## ZOOM ON THE PRODUCT

A system that give the feeling to the consumer to take part in the ultimate process

Possibility to have a nomad pack with a closure system

Possibility to have a nomad pack with a closure system

For aqueous formulations from 1 to 3000 centipoises



Outflow Outflow

Ø2,8

Ø1.2

Packaging delivered in 3 parts (a ampoule with an integrated applicator tip, a tank and a valve)

Available with different applicator tips adapted to your formulas

Ŧ

- A Integrated applicator tip B Headwear applicator tip

#### The Ariane Pack allows two formulations to be activated at the time of use:

- 1 Remove tamper tab
- 2 Hit the tank to release the active product: powder or liquid
- 3 Shack the pack
- 4 Snap the head of the ampoule
- 5 Apply pressure on the cap to distribute the product : drip or larger dose







**DECORATION** Screen (silk) printing Hot stamping


#### **ARIANE**

## PUMP PACK: 2 FORMULATIONS TO MIX



The Ariane Pack allows two formulations to be activated at the time of use:

- 1 Remove tamper tab
- 2 Hit the tank to release the active product: powder or liquid
- 3 Shack the pack
- 4 Apply pressure on the pump to distribute the product



# **ZOOM**ON THE PRODUCT

A system that give the feeling to the consumer to take part in the ultimate process

Available in cream or spray version, dose from 130µl or 230µl

Product distribution with a viscosity from 1 to 30000 centipoises





#### DISTRIBUTION

Liquids Serum Cream Powders








#### **DECORATION**

Screen (silk) printing Hot stamping Offset

## AIRLESS WELDED

Ø21 - Ø32 - Ø41



## Ø 32-M17



15 ml 20 ml △ PP/Others A PP/Others 30 ml A PP/Others

40 ml A PP/Others

50 ml A PP/Others

## ZOOM


#### ON THE PRODUCT

#### Dose of available pumps: 130µl to 450µl

Product distribution with a viscosity from 0 to 75000 centipoises

Possibility of using little or no preservatives





Packaging delivered in 2 or 3 parts (a bottle and a pump assembly with polished or frosted cap assembled or pump and cap)

Optimum use of the product, in case of very thick formulations, or sensitive to air

Pump efficiency guarantee to the latter pressure it is used upside down or head up

#### DISTRIBUTION

Cream Liquid Serum







#### **DECORATION**

Screen (silk) printing Hot stamping

#### PACK PREMIA

Ø32 AIRLESS

#### AIRLESS - ATMOSPHERIC



#### Ø 32 ATMOSPHERIC




## ZOOM

#### ON THE PRODUCT

Packaging delivered in 3 parts (A pack consisting of a bottle embedded in a crystal shell secured by a ring, a pump and a crystal cap)

Dose of available pumps: 150µl and 250µl



#### Airless



Essential Premium

Elite

## **AIRLESS:**

Pump efficiency guarantee to the latter pressure it is used upside down or head up

Optimum use of the product, in case of very thick formulations, or sensitive to air

Possibility of using little or no preservatives

Product distribution with a viscosity from 3000 to 75000 centipoises

#### **Atmospheric**



Essential Premium

#### **ATMOSPHERIC:**

Product distribution with a viscosity from 1 to 30000 centipoises

Three design pumps out flow: pump essential, pump premium and pompe elite

SOIN DE

#### **DISTRIBUTION**

Cream Liquid Serum









Mercei

## **PRESTIGE** GLASS POLYMER PACKAGING

## Ø 28 SQUARE



#### Ø 32 CYLINDRICAL



## △ PETG/Others

30 ml △ PETG/Others

## ZOOM

#### ON THE PRODUCT

Ring: plastic or métal

Pipette: Shells alu, glass or plastic **Dropper:** different possibilities of tips

Screwing 18-400


Distribution with pump or with dropper

Product distribution with a viscosity from 1 to 30000 centipoises





Premium



#### **SQUARE PRESTIGE BOTTLES:**

Packaging delivered in 2 parts: a bottle and a pump or a dropper

Essential

#### **CYLINDRICAL PRESTIGE BOTTLES:**



Packaging delivered in 2 or 3 parts: a bottle and a pump + a cap or a dropper with or without cap

Material Glass imitation

#### DISTRIBUTION

Cream Liquid

Serum






**DECORATION** Screen (silk) printing Hot stamping

## ATMOSPHERIC WELDED

Ø21-M19






Packaging delivered in 2 parts (a bottle, a pump assembly with assembled cap polished)

Dose of available pumps: 130µl or 230µl

Product distribution with a viscosity from 1 to 30000 centipoises

Cream or spray pumps











## ATMOSPHERIC WELDED

Ø32 - Ø41 - M17

Ø 32



ZOOM


## ON THE PRODUCT

Packaging delivered in 3 parts (a bottle, a pump and polished or frosted cap)

Various caps: smooth or frosted, right, rounded

Dose of available pumps: 150µl or 250µl

Product distribution with a viscosity from 1 to 30000 centipoises



#### Atmospheric







Essential

Premium

Elite

#### Ø41



DISTRIBUTION

Cream






Screen (silk) printing
Hot stamping



## **ATMOSPHERIC**

Ø32 - Ø41 - Ø52 - FEA 20




## ZOOM ON THE PRODUCT

Packaging delivered in 3 parts (a bottle, a pump and polished or frosted cap)

Various caps: smooth or frosted, right, rounded

Dose of available pumps: 150µl



Ø 41



△ PP/others



75 ml △ PP/others



100 ml △ PP/others



△ PP/others



150 ml △ PP/others



Color(s) of ring(s): Shiny silver, shiny gold

Product distribution with a viscosity from 1 to 30000 centipoises

Ø 52



100 ml A PP/others



△ PP/others

150 ml

△ PP/others



250 ml △ PP/others A PP/others









#### **DECORATION**

Screen (silk) printing Hot stamping

## **ATMOSPHERIC**

22-400 / 24-410 Ø52 24-410









75 ml A PP/Others



100 ml A PP/Others



125 ml A PP/Others



## ZOOM

## ON THE PRODUCT

Packaging delivered in 3 parts (a bottle, a pump and polished or frosted cap)

Various caps: smooth or frosted, right, rounded

For pumps 22-400 / 24-410


Dose of available pumps: 190µl to 450µl

Product distribution with a viscosity from 1 to 30000 centipoises



22-400

24-410





22-400

#### 24-410







Ø 52



100 ml









150 ml △ PP/Others



200 ml △ PP/Others



250 ml A PP/Others



**DISTRIBUTION** 

Spray

Cream





#### **DECORATION**

Screen (silk) printing Hot stamping

## **ERGOPACK**

△ PP/Others △ PP/Others

Ø32 - Ø41





Packaging delivered in 2 parts (a bottle, a pump assembly with assembled cap)

Quick filling with its wide opening

Customizing the pack with a wide range of bottles, polished and frosted caps: curved or straight

Various caps: smooth or frosted, right, rounded

Product distribution with a viscosity from 1 to 30000 centipoises

Dose of available pumps: 190µl to 450µl









Ø32 Cream



Ø41 Spray



Ø41 Cream



A PP/Others

A PP/Others

A PP/Others


△ PP/Others

# DISTRIBUTION Spray Cream



# DECORATION Screen (silk) printing Hot stamping

#### **FOAMER**



# **ZOOM**ON THE PRODUCT


#### **EASY** to actuate

**2 diameters:** Ø35 and Ø48

Quick filling with its wide opening

Create a propellant-free foam with a simple pump gesture





Dose of available pumps:

**50ml** : 400µl **150ml** : 750µl

Packaging delivered in 2 parts:
a bole and a screw pump assembly

exper!

DECORATION
Screen (silk) printing
Hot stamping

SOIN DE

with assembled cap



#### PILL BOX POWDERING DEVICE

Ø32 - Ø41 - Ø52

Ø 32



50 ml


93

Ø 41





ZOOM


ON THE PRODUCT



Wide range of tamper-proof capsules: pills with or without seal, powder 1 hole, 4 holes or 5 holes









Quick filling with its wide opening

Packaging delivered in 2 parts (a bottle and a dispensing capsule)

Wide range of capacities over 3 diameters (32/41/52)



Ø 52



**DISTRIBUTION** 

Powders Granules








DECORATION


Screen (silk) printing Hot stamping Offset

## SOFT APLLICATOR

Ø41

Ø 41





# **ZOOM**ON THE PRODUCT

#### Quick filling with its wide opening

Product distribution with a viscosity from 3000 to 30000 centipoises

Easy to use by pressing on the body of the bottle










Screen (silk) printing
Hot stamping

#### REFILLIABLE BOTTLE

AIRLESS - ATMOSPHERIC





## ZOOM

#### ON THE PRODUCT

Packaging delivered in 2 parts:
A shell (a pump assembled on a shell + a cap).
A refill bottle with integrated piston
(for airless bottle) or with integrated dip tube
(for atmospheric bottle)

Dose of available pumps: 150µl and 250µl

# AIRLESS

**ATMOSPHÉRIC** 

#### Airless



#### **Atmospheric**



#### **AIRLESS:**

Pump efficiency guarantee to the latter pressure it is used upside down or head up

Optimum use of the product, in case of very thick formulations, or sensitive to air

Possibility of using little or no preservatives

Product distribution with a viscosity from 3000 to 75000 centipoises

#### **ATMOSPHERIC:**

Product distribution with a viscosity from 1 to 30000 centipoises

Three design pumps out flow: pump essential, pump premium and pompe elite

#### DISTRIBUTION

Cream Liquid Serum





## DECORATION

Screen (silk) printing
Hot stamping
Offset